



LED PAR30 S/L

10PAR30L/AMB/830/F40/GL/D ULW BC 1PK 4/1

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	25,000
Rated Lifetime (Hours)	25,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	850 lm
Luminous Intensity (Nom)	1,600 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	85.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	10 W


Lamp Current (Nom)	86 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	172 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
EyeComfort	Yes
Product Data	
Order product name	10PAR30L/AMB/830/F40/GL/D ULW BC 1PK
	4/1

LED PAR30 S/L

Full product name	10PAR30L/AMB/830/F40/GL/D ULW BC 1PK 4/1
Order code	471300
Material Nr. (12NC)	929001322103
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	046677471309
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677471304

Dimensional drawing




Product	D	C
10PAR30L/AMB/830/F40/GL/D ULW BC 1PK 4/1	3-3/4 inch	4-11/16 inch


Photometric data



Light Distribution Diagram - 10PAR30L/AMB/830/F40/GL/D ULW BC 1PK
4/1




Spectral Power Distribution Colour - 10PAR30L/AMB/830/F40/GL/D ULW
BC 1PK 4/1




Accent Lighting Spots - 10PAR30L/AMB/830/F40/GL/D ULW BC 1PK 4/1

LED PAR30 S/L

Lifetime



Life Expectancy Diagram - 10PAR30L/AMB/830/F40/GL/D ULW BC 1PK 4/1



Lumen Maintenance Diagram - 10PAR30L/AMB/830/F40/GL/D ULW BC 1PK 4/1

