



MASTER LEDspot PAR

MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Product data


General Information		Luminous Flux in 90° Cone (Rated)	
Cap base	E27 [E27]		820 lm
Nominal lifetime (nom.)	25000 h	Operating and Electrical	
Technical type	9.5-75W	Input frequency	50 Hz
Light Technical		Power (Rated) (Nom)	9.5 W
Colour code	841 [CCT of 4100K (841)]	Lamp current (nom.)	48 mA
Beam Angle (Nom)	25 °	Wattage equivalent	75 W
Luminous flux (nom.)	820 lm	Starting time (nom.)	0.5 s
Luminous intensity (nom.)	3500 cd	Warm-up time to 60% light (nom.)	0.5 s
Colour designation	Cool White (CW)	Power factor (nom.)	0.85
Correlated colour temperature (nom.)	4000 K	Voltage (Nom)	220-240 V
Luminous efficacy (rated) (nom.)	92.63 lm/W	Controls and Dimming	
Colour consistency	<6	Dimmable	Yes
Colour rendering index (nom.)	80	Approval and Application	
LLMF at end of nominal lifetime (nom.)	70 %	Energy efficiency label (EEL)	A+

MASTER LEDspot PAR

Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	10 kWh
Product Data	
Full product code	871869671384600
Order product name	MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D
EAN/UPC – product	8718696713846

Order code	71384600
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001323002
Net weight (piece)	0.230 kg


Dimensional drawing




PAR30s 220-240V 9-75W 4000K E27 D

Product	D	C
MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D	95 mm	86 mm


Photometric data



MASTER LEDspot PAR 75W E27 840 25D





MASTER LEDspot PAR 75W E27 840 25D



MASTER LEDspot PAR 75W E27 840 25D

MASTER LEDspot PAR

Lifetime



MASTER LEDspot PAR 50W E27 827 25D

MASTER LEDspot PAR 50W E27 827 25D

