



# MASTER LEDspot PAR

## MAS LEDspot D 9-70W E27 927 PAR30S 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

### Product data

General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	25000 h
Switching cycle	25,000X
Technical type	9-70W
Light Technical	
Colour code	927
Beam Angle (Nom)	25 °
Luminous flux (nom.)	630 lm
Luminous intensity (nom.)	3000 cd
Colour designation	Warm White (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	66.32 lm/W
Colour consistency	<6
Color rendering index (nom.)	90

LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	9 W
Lamp current (nom.)	48 mA
Wattage equivalent	70 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.85
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C

# MASTER LEDspot PAR

## Controls and Dimming

Dimmable	Yes
----------	-----

## Approval and Application

Energy efficiency label (EEL)	A+
-------------------------------	----

Suitable for accent lighting	Yes
------------------------------	-----

Energy Consumption kWh/1000 h	9 kWh
-------------------------------	-------

## Product Data

Full product code	871869671412600
-------------------	-----------------

Order product name	MAS LEDspot D 9-70W E27 927 PAR30S 25D
--------------------	--

EAN/UPC – product	8718696714126
-------------------	---------------

Order code	71412600
------------	----------


Numerator – quantity per pack	1
-------------------------------	---

Numerator – packs per outer box	6
---------------------------------	---

Material no. (12NC)	929001323108
---------------------	--------------

Net weight (piece)	0.220 kg
--------------------	----------

## Dimensional drawing



PAR30s 220-240V 8-75W 2700K E27 D

Product	D	C
MAS LEDspot D 9-70W E27 927 PAR30S 25D	95 mm	86 mm

