



# MASTER LEDspot PAR

## MAS LEDspot D 9-70W E27 927 PAR30S 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

### Product data

General Information	
Cap base	E27 [ E27]
Nominal lifetime (nom.)	25000 h
Technical type	9-70W
Light Technical	
Colour Code	927
Technical Beam Angle (Nom)	25 °
Lamp Luminous Flux 25°C EL (Nom)	630 lm
Luminous intensity (nom.)	3000 cd
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	66.32 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	90
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	9 W
Lamp current (nom.)	48 mA
Wattage equivalent	70 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.85
Voltage (Nom)	220-240 V


Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes

# MASTER LEDspot PAR

Energy Consumption kWh/1000 h	9 kWh
<b>Product Data</b>	
Full product code	871869671412600
Order product name	MAS LEDspot D 9-70W E27 927 PAR30S 25D
EAN/UPC – product	8718696714126
Order code	929001323108

Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001323108
Net weight (piece)	0.220 kg

## Dimensional drawing



PAR30s 220-240V 8-75W 2700K E27 D

Product	D	C
MAS LEDspot D 9-70W E27 927 PAR30S 25D	95 mm	86 mm

