



# CorePro LEDcapsule MV

## CorePro LEDcapsule ND 1.9-25W G9 827

This single-ended mains-voltage capsule for G9-base luminaires delivers directional light, making it a true alternative to halogen capsule lamps. It is particularly suitable for task lighting in shops, hotels and restaurants, and ideal for desk lamps and cabinet lighting. Compatible with existing fixtures with G9 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs, without any compromise on light quality.

### Product data

General Information		Lamp current (nom.)	
Cap base	G9 [ G9]		18 mA
Nominal lifetime (nom.)	15000 h	Wattage equivalent	25 W
Switching cycle	30000X	Starting time (nom.)	0.5 s
Technical type	1.9-25W	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Colour code	827 [ CCT of 2,700 K]	T-Case maximum (nom.)	60 °C
Luminous flux (nom.)	204 lm		
Colour designation	Warm white (WW)	Controls and Dimming	
Correlated colour temperature (nom.)	2700 K	Dimmable	No
Luminous efficacy (rated) (nom.)	107.37 lm/W	Approval and Application	
Colour consistency	<6	Energy efficiency label (EEL)	A++
Color rendering index (nom.)	80	Energy Consumption kWh/1000 h	2 kWh
LLMF at end of nominal lifetime (nom.)	70 %	Product Data	
Operating and Electrical		Full product code	871869671392100
Input frequency	50 Hz		
Power (Rated) (Nom)	1.9 W		

# CorePro LEDcapsule MV

Order product name	CorePro LEDcapsule ND 1.9-25W G9 827
EAN/UPC – product	8718696713921
Order code	71392100
Numerator – quantity per pack	1
Numerator – packs per outer box	12


Material no. (12NC)	929001323802
Net weight (piece)	0.012 kg

## Dimensional drawing


Product	D	C
CorePro LEDcapsule ND 1.9-25W G9 827	16.5 mm	48 mm

G9 230V 2.5W-25W 204lm 2700K G9 Non-Dim

## Photometric data




General Information E1 Photometry E1 Page 10



CorePro LEDcapsule MV 25W G9 827 Capsule

CorePro LEDcapsule MV 25W G9 827 Capsule



CorePro LEDcapsule MV 25W G9 827 Capsule

# CorePro LEDcapsule MV

## Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

