



Classic filament LED candles and lusters

Classic LEDLUSTER D 2.7-25W P45 E27 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data


General Information			
Cap-Base	E27 [E27]	Power Consumption	2.7 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	12 mA
Switching Cycle	20,000	Wattage Equivalent	25 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	104 °F
Luminous Flux	250 lm		
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	92.59 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	P45 [P 45mm]
Operating and Electrical		Approval and Application	
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	3 kWh
Input Frequency	50 to 60 Hz		

Classic filament LED candles and lusters

EyeComfort	Yes
Product Data	
Order product name	CLA LEDLuster D 2.7-25W P45 E27 827 CL
Full product name	Classic LEDLUSTER D 2.7-25W P45 E27 827 CL
Full product code	871869670988700
Order code	362715


Material Nr. (12NC)	929001332402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696709887
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696709894

Dimensional drawing




Product	D	C
CLA LEDLuster D 2.7-25W P45 E27 827 CL	1-13/16 inch	3-3/16 inch


Photometric data



Spectral Power Distribution Colour - CLA LEDLuster D 2.7-25W P45 E27 827 CL




General uniform lighting - CLA LEDLuster D 2.7-25W P45 E27 827 CL




Light Distribution Diagram - CLA LEDLuster D 2.7-25W P45 E27 827 CL

Classic filament LED candles and lusters

Lifetime



Life Expectancy Diagram - CLA LEDLuster D 2.7-25W P45 E27 827 CL



Lumen Maintenance Diagram - CLA LEDLuster D 2.7-25W P45 E27 827 CL

