



MASTER LEDspot ExpertColor LV

MASTER LED ExpertColor LED MR16 ExpertColor 7.2-50W 930 60D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customised spectrum, high CRI and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Product data


General Information	
Cap base	GU5.3 [GU5.3]
Nominal lifetime (nom.)	40000 h
Switching cycle	50000X
Technical type	7.2-50W
Light Technical	
Colour Code	930 [CCT of 3,000 K]
Technical Beam Angle (Nom)	60 °
Lamp Luminous Flux 25°C EL (Nom)	480 lm
Luminous intensity (nom.)	440 cd
Colour Designation	White (WH)
Colour Temperature, horizontal (Nom)	3000 K
Lamp Luminous Efficacy EM (Nom)	66.67 lm/W
Colour consistency	<3
Colour Rendering Index, horiz (Nom)	97

LLMF at end of nominal lifetime (nom.) 70 %	
Operating and Electrical	
Power (Rated) (Nom)	7.2 W
Lamp current (nom.)	800 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	1 s
Power factor (nom.)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case maximum (nom.)	92 °C

MASTER LEDspot ExpertColor LV


Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	Not applicable
Suitable for accent lighting	Yes
Product Data	
Full product code	871869671952700
Order product name	MASTER LED ExpertColor LED MR16 ExpertColor 7.2-50W 930 60D

Dimensional drawing



MAS LED MR16 ExpertColor 7.2-50W 930 60D


Photometric data



Master LEDspot ExpertColor LV 50W EZ10 930 10D

EAN/UPC – product	8718696719527
Order code	929001341508
Local Code	MEC480LMR1660D
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001341508
Net weight (piece)	0.034 kg


Product	D	C
MASTER LED ExpertColor LED MR16 ExpertColor 7.2-50W 930 60D	50.5 mm	46 mm



Master LEDspot ExpertColor LV 50W GU5.3 930 60D


MASTER LEDspot ExpertColor LV

Photometric data




Master LEDspot ExpertColor LV 50W GU5.3 930 60D

Lifetime



Master LEDspot ExpertColor LV 50W EZ10 927 10D



Master LEDspot ExpertColor LV 50W EZ10 927 10D

