



MASTER LEDspot ExpertColor LV

MASTER LED ExpertColor 6.5-35W MR16 927 10D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Product data

General Information		
Cap-Base	GU5.3 [GU5.3]	
Nominal lifetime	40,000 hour(s)	
Switching Cycle	50,000	
Lighting Technology	LED	
EU RoHS compliant	Yes	
Light Technical		
Color Code	927	
Beam Angle (Nom)	10 degree(s)	
Luminous Flux	410 lm	
Luminous Intensity (Nom)	4,600 cd	
Color Designation	Warm White (WW)	
Correlated Color Temperature (Nom)	2700 K	
Luminous Efficacy (rated) (Nom)	63.00 lm/W	
Color Consistency	<3	
Color rendering index (CRI)	97	
LLMF At End Of Nominal Lifetime (Nom) 70 %		

Luminous Flux in 90° Cone (Rated)	410 lm
Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	6.5 W
Lamp Current (Nom)	800 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	90 ℃


Datasheet, 2023, April 29 data subject to change

MASTER LEDspot ExpertColor LV

Controls and Dimming	·
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	8 kWh
EyeComfort	Yes
Product Data	
Order product name	MAS LED ExpertColor 6 5-35W MR16 927 10D


Full product name	MASTER LED ExpertColor 6.5-35W MR16 927
	10D
Full product code	871869673871900
Order code	73871900
Material Nr. (12NC)	929001341702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696738719
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696738726


Dimensional drawing




Product	D	С
MAS LED ExpertColor 6.5-35W MR16 927 10D	51 mm	46 mm

Photometric data








Accent Lighting Spots - MAS LED ExpertColor 6.5-35W MR16 927 10D


MASTER LEDspot ExpertColor LV


Photometric data



Light Distribution Diagram - MAS LED ExpertColor 6.5-35W MR16 927 10D

Lifetime





Life Expectancy Diagram - MAS LED ExpertColor 6.5-35W MR16 927 10D

Lumen Maintenance Diagram - MAS LED ExpertColor 6.5-35W MR16 927 10D



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.