



# MASTER LEDspot ExpertColor LV

## MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 930 36D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

### Product data

General Information	
Cap-Base	GU5.3 [ GU5.3]
Nominal Lifetime (Nom)	40000 h
Switching Cycle	50000X
Technical Type	6.5-35W
Light Technical	
Colour Code	930 [ CCT of 3000K]
Beam Angle (Nom)	36 °
Luminous Flux (Nom)	440 lm
Luminous Flux (Rated) (Nom)	440 lm
Luminous Intensity (Nom)	1400 cd
Colour Designation	White (WH)
Rated Beam Angle	36 °
Colour Temperature, horizontal (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	67.69 lm/W

Color Consistency	<3
Colour Rendering Index horiz (Nom)	97
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	440 lm
Operating and Electrical	
Power (Rated) (Nom)	6.5 W
Lamp Current (Nom)	800 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	ac electronic 12 V

# MASTER LEDspot ExpertColor LV

## Temperature

T-Case Maximum (Nom)	90 °C
----------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Approval and Application


Energy Efficiency Label	A+
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	8 kWh

## Product Data

Full product code	871869673885600
-------------------	-----------------

Order product name	MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 930 36D
EAN/UPC - Product	8718696738856
Order code	73885600
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001342402
Net Weight (Piece)	0.030 kg



## Dimensional drawing



MR16 12V 6.5-42W 450lm 35D 3000K GU5.3 D

Product	D	C
MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 930 36D	51 mm	46 mm

## Photometric data




MR16 12V 6.5-42W 450lm 35D 3000K GU5.3 D

LEDSpots MR16 7W 930 460lm 35D


# MASTER LEDspot ExpertColor LV

## Photometric data




LEDspots MR16 7W 3000K

## Lifetime



LEDspots MR16 7W



LEDspots MR16 7W

