



# CorePro LED PLC

## CorePro LED PLC 4.5W 830 2P G24d-1

Philips CorePro LED PLC is the ideal uplampping solution for downlights in a wide range of general lighting applications. It integrates a LED light source into a traditional fluorescent form factor to offer superb energy savings over a lifetime that's twice as long as fluorescent alternatives.

### Product data

General Information	
Cap-Base	G24D-1 [ G24d-1]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	30000 h
Switching Cycle	50000X
Light Technical	
Color Code	830 [ CCT of 3000K]
Luminous Flux (Nom)	475 lm
Correlated Color Temperature (Nom)	3000 K
Color Consistency	<6
Color Rendering Index (Nom)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	4.5 W
Lamp Current (Max)	25 mA
Lamp Current (Min)	20 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9

Voltage (Nom)	220-240 V
Temperature	
T-Ambient (Max)	35 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	100 mm
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	5 kWh

# CorePro LED PLC


## Product Data

Full product code	871869670659600
Order product name	CorePro LED PLC 4.5W 830 2P G24d-1
EAN/UPC - Product	8718696706596
Order code	929001350702
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001350702
Net Weight (Piece)	0.070 kg

## Warnings and Safety


## Dimensional drawing



PLED PLC 230V 5W 450lm 3000K G24D-1 ND


Product	D1	D2	A1	A2	A3
CorePro LED PLC 4.5W 830 2P G24d-1	24.3 mm	28.4 mm	95.8 mm	115 mm	137.6 mm

## Photometric data




General Information 11 Photometry 11 Page 11

CorePro LED PLC 100mm 5W G24D-1 830 475lm




LEDtube 100mm 5W G24D-1 830 475lm



LEDtube 100mm 5W G24D-1

# CorePro LED PLC

## Lifetime



LEDtube 100mm 5W G24D-1

LEDtube 100mm 5W G24D-1

