

MASTER LEDspot PAR High Lumen

Master LED PAR30L 20W 15D 840

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	15 degree(s)
Luminous Flux	1,850 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	92.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	20 W
Lamp Current (Nom)	95 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	67 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]

Approval and Application	
Suitable For Accent Lighting	Yes

MASTER LEDspot PAR High Lumen


Energy Consumption kWh/1000 h	20 kWh

Material Nr. (12NC)	929001353908
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696731291
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696731307

Product Data


Order product name	Master LED PAR30L 20W 15D 840
Full product name	Master LED PAR30L 20W 15D 840
Full product code	871869673129100
Order code	929001353908

Dimensional drawing




Product	D	C
Master LED PAR30L 20W 15D 840	95.5 mm	129 mm


Photometric data



Light Distribution Diagram - Master LED PAR30L 20W 15D 840




Accent Lighting Spots - Master LED PAR30L 20W 15D 840




Spectral Power Distribution Colour - Master LED PAR30L 20W 15D 840

MASTER LEDspot PAR High Lumen

Lifetime



Life Expectancy Diagram - Master LED PAR30L 20W 15D 840



Lumen Maintenance Diagram - Master LED PAR30L 20W 15D 840

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.