



MASTER LEDspot PAR High Lumen

Master LED PAR30L 20W 30D 840

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high-efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high-performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

Product data


General Information		Lamp current (nom.)	
Cap base	E27 [E27]		95 mA
Nominal lifetime (nom.)	25000 h	Wattage equivalent	35 W
Switching cycle	50000X	Starting time (nom.)	0.5 s
Technical type	20-35W	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.9
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Colour Code	840 [CCT of 4,000 K]	T-Case maximum (nom.)	67 °C
Technical Beam Angle (Nom)	30 °		
Lamp Luminous Flux 25°C EL (Nom)	1850 lm	Controls and Dimming	
Colour Designation	Cool White (CW)	Dimmable	No
Colour Temperature, horizontal (Nom)	4000 K		
Lamp Luminous Efficacy EM (Nom)	92.00 lm/W	Approval and Application	
Colour consistency	<6	Energy efficiency label (EEL)	A+
Colour Rendering Index,horiz (Nom)	82	Suitable for accent lighting	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Energy Consumption kWh/1000 h	20 kWh
Operating and Electrical		Product Data	
Input frequency	50 to 60 Hz	Full product code	871869673136900
Power (Rated) (Nom)	20 W		

MASTER LEDspot PAR High Lumen

Order product name	Master LED PAR30L 20W 30D 840
EAN/UPC – product	8718696731369
Order code	73136900
Numerator – quantity per pack	1
Numerator – packs per outer box	6

Material no. (12NC)	929001354108
Net weight (piece)	0.410 kg


Dimensional drawing




PAR30L 220–240V 20–35W 1850lm 4KK E27 ND

Product	D	C
Master LED PAR30L 20W 30D 840	95.5 mm	129 mm


Photometric data



LEDspot PAR30L E27 20W 4000K 30D



LEDspot PAR30L E27 20W 4000K 30D



LEDspot PAR30L E27 4000K 30D

MASTER LEDspot PAR High Lumen

Lifetime



LEDspot MAS 37W E27 PAR30L 830 15D ND



LEDspot MAS 37W E27 PAR30L 830 15D ND

