



MASTER LEDspot PAR High Lumen

Master LED PAR30L 32W 15D 840

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high-efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high-performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	32-50W
Light Technical	
Colour Code	840 [CCT of 4,000 K]
Technical Beam Angle (Nom)	15 °
Lamp Luminous Flux 25°C EL (Nom)	3000 lm
Colour Designation	Cool White (CW)
Colour Temperature, horizontal (Nom)	4000 K
Lamp Luminous Efficacy EM (Nom)	93.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	82
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	32 W


Lamp current (nom.)	160 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	79 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	32 kWh
Product Data	
Full product code	871869673140600

MASTER LEDspot PAR High Lumen

Order product name	Master LED PAR30L 32W 15D 840
EAN/UPC – product	8718696731406
Order code	929001354408
Numerator – quantity per pack	1
Numerator – packs per outer box	6

Material no. (12NC)	929001354408
Net weight (piece)	0.410 kg


Dimensional drawing




PAR30L 220-240V 32-70W 15D 4000K E27 ND

Product	D	C
Master LED PAR30L 32W 15D 840	95.5 mm	129 mm


Photometric data



LEDspot PAR30L E27 32W 4000K 15D



LEDspot PAR30L E27 4000K 15D



LEDspot PAR30L E27 32W 4000K 15D

MASTER LEDspot PAR High Lumen

Lifetime



LEDspot MAS 37W E27 PAR30L 830 15D ND



LEDspot MAS 37W E27 PAR30L 830 15D ND

