



# TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

## TrueForce LED HPI ND 200-145W E40 840 60D

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in High-bay applications. The solution gives you the LED benefits of energy-efficiency and long-lifetime, plus the initial investment is low. With unique lamp design and compatibility, you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear. Multiple beam angle options and high colour-rendering index enhance the lighting distribution while creating a comfortable, safe and high-productivity environment.

### Product data

General Information	
Cap base	E40 [ E40]
RoHS mark	RoHS mark
Nominal lifetime (nom.)	50000 h
Switching cycle	50000X
Technical type	145-400W

Light Technical	
Colour code	840 [ CCT of 4,000 K]
Beam Angle (Nom)	60 °
Luminous flux (nom.)	20000 lm
Luminous flux (rated) (nom.)	20000 lm

Colour designation	Cool White (CW)
Correlated colour temperature (nom.)	4000 K
Luminous efficacy (rated) (nom.)	137.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 Hz
Power (Rated) (Nom)	145 W
Lamp current (nom.)	3900 mA
Wattage equivalent	400 W

# TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Starting time (nom.)	0.7 s
Warm-up time to 60% light (nom.)	0.7 s
Power factor (nom.)	0.7
Voltage (Nom)	100-145 V

## Temperature

T-Case maximum (nom.)	95 °C
-----------------------	-------

## Controls and Dimming

Dimmable	No
----------	----

## Approval and Application

Ingress protection code	IP40 [ Wire-protected]
Energy efficiency label (EEL)	A+

Energy Consumption kWh/1000 h	160 kWh
-------------------------------	---------


## Product Data

Full product code	871869671386000
Order product name	TrueForce LED HPI ND 200-145W E40 840 60D
EAN/UPC – product	8718696713860
Order code	71386000
Numerator – quantity per pack	1
Numerator – packs per outer box	2
Material no. (12NC)	929001357002
Net weight (piece)	1.300 kg



## Warnings and Safety


### Dimensional drawing



TForce LED HIL ND 150-400W E40 840 60D


Product	D	C
TrueForce LED HPI ND 200-145W E40 840 60D	210 mm	250 mm

### Photometric data



General Uniform Lighting  
 Technical Data Sheet  
 Page 17


400W E40 Others ND 60D 840 4000K



400W E40 Others ND 60D 840 4000K


# TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

## Photometric data




400W E40 Others ND

## Lifetime



400W E40 Others ND



LedTrueForce

