



# MASTER LEDspot PAR

## Master LED PAR30L 40W 30D 827

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

### Product data

General Information	
Cap-Base	E27 [ E27]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	40-70W
Light Technical	
Color Code	827 [ CCT of 2700K]
Beam Angle (Nom)	30 °
Luminous Flux (Nom)	4300 lm
Luminous Flux (Rated) (Nom)	4300 lm
Luminous Intensity (Nom)	13000 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	107.00 lm/W
Color Consistency	<6

Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	40 W
Lamp Current (Nom)	196 mA
Wattage Equivalent	70 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	90 °C

# MASTER LEDspot PAR

## Controls and Dimming

Dimmable	No
----------	----

## Approval and Application


Energy Efficiency Label (EEL)	A+
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	40 kWh

## Product Data

Full product code	871869675939400
-------------------	-----------------

Order product name	Master LED PAR30L 40W 30D 827
EAN/UPC - Product	8718696759394
Order code	929001374708
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001374708
Net Weight (Piece)	0.410 kg


## Dimensional drawing




PAR30L 40-35W 4500lm 30D 2700K E27 ND

Product	D	C
Master LED PAR30L 40W 30D 827	95.5 mm	129 mm

## Photometric data



LEDspot MAS 41W E27 PAR30L 827 30D ND



LEDspot MAS 41W E27 PAR30L 827 30D ND

