



MASTER LEDspot PAR

Master LED PAR30L 40W 30D 840

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	40-70W
Light Technical	
Colour Code	840 [CCT of 4,000 K]
Technical Beam Angle (Nom)	30 °
Lamp Luminous Flux 25°C EL (Nom)	4600 lm
Luminous intensity (nom.)	14000 cd
Colour Designation	Cool White (CW)
Colour Temperature, horizontal (Nom)	4000 K
Lamp Luminous Efficacy EM (Nom)	115.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	82

LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	40 W
Lamp current (nom.)	196 mA
Wattage equivalent	70 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	90 °C

MASTER LEDspot PAR

Controls and Dimming

Dimmable	No
----------	----

Approval and Application


Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	40 kWh

Product Data

Full product code	871869675945500
-------------------	-----------------

Order product name	Master LED PAR30L 40W 30D 840
EAN/UPC – product	8718696759455
Order code	929001374908
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001374908
Net weight (piece)	0.410 kg


Dimensional drawing




PAR30L 40-35W 4500lm 30D 4000K E27 ND

Product	D	C
Master LED PAR30L 40W 30D 840	95.5 mm	129 mm

Photometric data





LEDspot E27 PAR30L 40W 4000K



LEDspot E27 PAR30L 40W 4000K

MASTER LEDspot PAR

Lifetime



LEDspot E27 PAR30L 35W 4000K

LEDspot E27 PAR30L 35W 4000K

