



Essential LEDtube

CorePro LEDtube 600mm 8W840 G5 I APR

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data


General Information			
Cap-Base	G5 [G5]	Lamp Current (Min)	39 mA
Nominal lifetime	30,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.92
EU RoHS compliant	Yes	Voltage (Nom)	100-240 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	Ambient temperature range	-20 °C to 45 °C
Beam Angle (Nom)	200 degree(s)	T-Case Maximum (Nom)	70 °C
Luminous Flux	1,050 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	131.00 lm/W	Product Length	600 mm
Color Consistency	<6	Bulb Shape	T5
Color rendering index (CRI)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product	Yes
Operating and Electrical		Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	8 kWh
Input Frequency	50 to 60 Hz		
Power Consumption	8 W		
Lamp Current (Max)	89 mA		

Essential LEDtube

Product Data	
Order product name	CorePro LEDtube 600mm 8W840 G5 I APR
Full product name	CorePro LEDtube 600mm 8W840 G5 I APR
Full product code	871869673198700
Order code	929001380708
Material Nr. (12NC)	929001380708



Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696731987
Numerator - Packs per outer box	20
EAN/UPC - Case	8718696731994

Dimensional drawing




Product	D1	D2	A1	A2	A3
CorePro LEDtube 600mm 8W840 G5 I APR	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm

Photometric data



General uniform lighting - CorePro LEDtube 600mm 8W840 G5 I APR



Spectral Power Distribution Colour - CorePro LEDtube 600mm 8W840 G5 I APR




Light Distribution Diagram - CorePro LEDtube 600mm 8W840 G5 I APR

Essential LEDtube


Lifetime




Life Expectancy Diagram - CorePro LEDtube 600mm 8W840 G5 I APR



Life Expectancy Diagram - CorePro LEDtube 600mm 8W840 G5 I APR



Life Expectancy Diagram - CorePro LEDtube 600mm 8W840 G5 I APR



Lumen Maintenance Diagram - CorePro LEDtube 600mm 8W840 G5 I APR

Lumen Maintenance Diagram - CorePro LEDtube 600mm 8W840 G5 I APR

Essential LEDtube

