



Essential LEDtube

CorePro LEDtube 1200mm 16W830 G5 I APR

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G5
Nominal lifetime	30,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	2,000 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	125.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	16 W
Lamp Current (Max)	177 mA


Lamp Current (Min)	77 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.92
Voltage (Nom)	100-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1,200 mm
Bulb Shape	T5
Approval and Application	
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh

Essential LEDtube

Product Data	
Order product name	CorePro LEDtube 1200mm 16W830 G5 I APR
Full product name	CorePro LEDtube 1200mm 16W830 G5 I APR
Full product code	871869673202100
Order code	929001380908
Material Nr. (12NC)	929001380908



Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696732021
Numerator - Packs per outer box	20
EAN/UPC - Case	8718696732038

Dimensional drawing




Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 16W830 G5 I APR	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm

Photometric data



General uniform lighting - CorePro LEDtube 1200mm 16W830 G5 I APR



Spectral Power Distribution Colour - CorePro LEDtube 1200mm 16W830 G5 I APR




Light Distribution Diagram - CorePro LEDtube 1200mm 16W830 G5 I APR

Essential LEDtube


Lifetime




Life Expectancy Diagram - CorePro LEDtube 1200mm 16W830 G5 I APR



Life Expectancy Diagram - CorePro LEDtube 1200mm 16W830 G5 I APR



Life Expectancy Diagram - CorePro LEDtube 1200mm 16W830 G5 I APR



Lumen Maintenance Diagram - CorePro LEDtube 1200mm 16W830 G5 I APR

Lumen Maintenance Diagram - CorePro LEDtube 1200mm 16W830 G5 I APR

Essential LEDtube

