



MASTER LEDspot ExpertColor LV

MASTER LED ExpertColor 7.5-43W MR16 927 36D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Product data

General Information		
- Cherat Information		
Cap-Base	GU5.3 [GU5.3]	
Nominal lifetime	40,000 hour(s)	
Switching Cycle	50,000	
Lighting Technology	LED	
EU RoHS compliant	Yes	
Light Technical		
Color Code	927	
Beam Angle (Nom)	36 degree(s)	
Luminous Flux	485 lm	
Luminous Intensity (Nom)	1,400 cd	
Color Designation	Warm White (WW)	
Correlated Color Temperature (Nom)	2700 K	
Luminous Efficacy (rated) (Nom)	64.67 lm/W	
Color Consistency	<3	
Color rendering index (CRI)	92	
LLMF At End Of Nominal Lifetime (Nom) 70 %		

Luminous Flux in 90° Cone (Rated)	485 lm
Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	7.5 W
Lamp Current (Nom)	880 mA
Wattage Equivalent	43 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	93 ℃


Datasheet, 2023, April 29 data subject to change

MASTER LEDspot ExpertColor LV

Controls and Dimming		
Dimmable	Yes	
Mechanical and Housing		
Bulb Shape	MR16 [2inch/50mm]	
Approval and Application		
Suitable For Accent Lighting	Yes	
Energy Consumption kWh/1000 h	9 kWh	
EyeComfort	Yes	
Product Data		
Order product name	MAS LED ExpertColor 7.5-43W MR16 927 36D	

Full product name	MASTER LED ExpertColor 7.5-43W MR16 927	
	36D	
Full product code	871869673544200	
Order code	73544200	
Material Nr. (12NC)	929001386302	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8718696735442	
Numerator - Packs per outer box	10	
EAN/UPC - Case	8718696735459	


Dimensional drawing




Product	D	С
MAS LED ExpertColor 7.5-43W MR16 927 36D	50.5 mm	46 mm

Photometric data








Light Distribution Diagram - MAS LED ExpertColor 7.5-43W MR16 927 36D


MASTER LEDspot ExpertColor LV


Photometric data



Spectral Power Distribution Colour - MAS LED ExpertColor 7.5-43W MR16 927 36D

Lifetime





Life Expectancy Diagram - MAS LED ExpertColor 7.5-43W MR16 927 36D

Lumen Maintenance Diagram - MAS LED ExpertColor 7.5-43W MR16 927



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.