



# LED Urban TrueForce Lamps

## 26ED23.5/LED/740/ND 120-277V G2 4/1

Philips TrueForce LED high lumen post top lamp makes it easy to upgrade to long lasting, energy saving LED technology without sacrificing your site's unique outdoor character. Philips TrueForce is a direct replacement option which ensures a perfect fit with existing modern and traditional luminaires. We claim true replacement when comparing flux. This post top lamps can be used in enclosed fixtures.

### Product data

General Information	
Cap-Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	26-70W
Light Technical	
Color Code	740 [ CCT of 4000K]
Beam Angle (Nom)	360 °
Luminous Flux (Nom)	3000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	115.00 lm/W
Color Consistency	ANSI 4000K
Color Rendering Index (Nom)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz


Power (Nom)	26 W
Lamp Current (Nom)	220 mA
Wattage Equivalent	70 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable

# LED Urban TrueForce Lamps

Energy Consumption kWh/1000 h	- kWh
<b>Product Data</b>	
Order product name	26ED23.5/LED/740/ND 120-277V G2 4/1
EAN/UPC - Product	046677473587
Order code	929001396304

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001396304
Net Weight (Piece)	0.365 kg



## Dimensional drawing



HIB NAM Post top 3000lm 4000K G2


Product	D	C
26ED23.5/LED/740/ND 120-277V G2 4/1	84 mm	176 mm

## Photometric data



HIB NAM Trueforce 26W E26 Clear 740 36D ND



HIB NAM Trueforce 26W E26 Clear 730 36D ND



HIB NAM Trueforce 26W-38W E26-E39 Clear 740 36D ND

# LED Urban TrueForce Lamps

## Lifetime



HIB NAM Trueforce 26W E26 Clear 730 36D ND

HIB NAM Trueforce 26W E26 Clear 730 36D ND

