

Premium LED candles & lusters Vintage Filament

LED classic 14W B35 E14 SP GOLD ND 1BC/4

Featuring a classic heritage design, the new Philips Vintage LED lamp family is reminiscent of familiar incandescent bulbs. Available in an array of giant shapes, candles and other familiar form factors, they provide a seamless fit across your space. When used as a statement piece, they add a sense of nostalgia and create a highly desirable atmosphere for socialization and relaxing.

Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	820 [CCT of 2000K]
Beam Angle (Nom)	280 degree(s)
Luminous Flux	125 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	54.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80


LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	2.3 W
Lamp Current (Nom)	22 mA
Wattage Equivalent	14 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	60 °C

Premium LED candles & lusters Vintage Filament

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Transparent amber
Bulb Shape	B35 [B 35mm]
Approval and Application	
Energy Consumption kWh/1000 h	3 kWh
Product Data	
Order product name	LED classic 14W B35 E14 SP GOLD ND 1BC/4

Full product name	LED classic 14W B35 E14 SP GOLD ND 1BC/4
Full product code	871869960671800
Order code	929001814542
Material Nr. (12NC)	929001814542
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699606718
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699606725

Dimensional drawing




Product	D	C
LED classic 14W B35 E14 SP GOLD ND 1BC/4	35 mm	99 mm

Photometric data




Spectral Power Distribution Colour - LED classic 14W B35 E14 SP GOLD ND 1BC/4



General uniform lighting - LED classic 14W B35 E14 SP GOLD ND 1BC/4


Premium LED candles & lusters Vintage Filament

Photometric data




Light Distribution Diagram - LED classic 14W B35 E14 SP GOLD ND 1BC/4

Lifetime



Life Expectancy Diagram - LED classic 14W B35 E14 SP GOLD ND 1BC/4



Lumen Maintenance Diagram - LED classic 14W B35 E14 SP GOLD ND 1BC/4

