

# Decorative LED bulbs

## LED classic-giant 25W E27 A160 GOLD ND

The new Deco collection (bulb) transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience. With very long lifetime, up to 90% energy savings, no flickering and an instant full-level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

### Product data

General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	5-25W
Light Technical	
Colour Code	820 [ CCT of 2,000 K]
Lamp Luminous Flux 25°C EL (Nom)	300 lm
Colour Designation	Flame
Colour Temperature, horizontal (Nom)	2000 K
Lamp Luminous Efficacy EM (Nom)	60.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	5 W
Lamp current (nom.)	44 mA
Wattage equivalent	25 W


Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	27 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Transparent Amber
Approval and Application	
Energy efficiency label (EEL)	A
Energy Consumption kWh/1000 h	5 kWh
Product Data	
Full product code	871869676806800
Order product name	LED classic-giant 25W E27 A160 GOLD ND
EAN/UPC – product	8718696768068

# Decorative LED bulbs

Order code	929001817101
Numerator – quantity per pack	1
Numerator – packs per outer box	2
Material no. (12NC)	929001817101

Net weight (piece)	0.230 kg
--------------------	----------



## Dimensional drawing



Bulb PS160 230V 6-25W 300lm 2000K E27 ND


Product	D	C
LED classic-giant 25W E27 A160 GOLD ND	160 mm	293 mm

## Photometric data



CLA LEDbulb 25W E27 820 GOLD A160



CLA LEDbulb 25W E27 820 GOLD A160



CLA LEDbulb 25W E27 820 GOLD A160

## Decorative LED bulbs

### Lifetime



LEDbulb 60W E14 827 FR B38

LEDbulb 60W E14 827 FR B38

