




MASTER Value Decorative LED bulbs

LED classic-giant 25W E27 G200 GOLD ND

The new collection of MASTER Value Decorative LED bulbs will transform any home. decorative LED bulbs are ideal for decorative lighting projects, they offer a perfect blend of (warm) white light and a minimalistic lighting experience. With a very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you can enjoy soft and evenly distributed light. And thanks to the dimmable LED bulbs, you can dial it up or down to suit your mood. So, you can create a welcoming harmony in your space with decorative LED lamps that shine with trendy and stylish charm.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	820 [CCT of 2000K]
Luminous Flux	300 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	60.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80


LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5 W
Lamp Current (Nom)	44 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	27 °C

MASTER Value Decorative LED bulbs

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Transparent amber
Bulb Shape	G200 [G 200mm]
Approval and Application	
Energy Consumption kWh/1000 h	5 kWh
EyeComfort	Yes
Product Data	
Order product name	LED classic-giant 25W E27 G200 GOLD ND



Full product name	LED classic-giant 25W E27 G200 GOLD ND
Full product code	871869676808200
Order code	76808200
Material Nr. (12NC)	929001817201
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696768082
Numerator - Packs per outer box	2
EAN/UPC - Case	8718696768099

Dimensional drawing



Product	D	C
LED classic-giant 25W E27 G200 GOLD ND	200 mm	286 mm

Photometric data




General uniform lighting - LED classic-giant 25W E27 G200 GOLD ND

Light Distribution Diagram - LED classic-giant 25W E27 G200 GOLD ND


MASTER Value Decorative LED bulbs

Photometric data




Spectral Power Distribution Colour - LED classic-giant 25W E27 G200 GOLD ND

Lifetime



Life Expectancy Diagram - LED classic-giant 25W E27 G200 GOLD ND



Lumen Maintenance Diagram - LED classic-giant 25W E27 G200 GOLD ND

