



# LED Highbay

## 150HB/LED/740/ND NB DL BB 2/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

### Product data


General Information	
Cap-Base	EX39 [ Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	150-400W
Light Technical	
Color Code	740 [ CCT of 4000K]
Beam Angle (Nom)	70 °
Luminous Flux (Nom)	20000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	133.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	150 W
Lamp Current (Nom)	1250 mA
Wattage Equivalent	400 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
UL Type	Type B - bypass the ballast
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard
Product Data	
Order product name	150HB/LED/740/ND NB DL BB 2/1
EAN/UPC - Product	046677478155
Order code	929001852904
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

# LED Highbay

Material Nr. (12NC)	929001852904
Net Weight (Piece)	0.880 kg


## Dimensional drawing




High Bay Mains 400W 4000K Down Light NB

Product	D	C
150HB/LED/740/ND NB DL BB 2/1	211 mm	252 mm


## Photometric data



TrueForce LED Industrial and Retail 740



TrueForce LED Industrial and Retail NB





Product Information 01 Page Lighting 01 Page 11

TrueForce LED Industrial and Retail 150HB 740 NB

# LED Highbay

## Lifetime



LED TForce HB MV 120-100W E40 others 840 12D ND NB

LED TForce HB MV 120-100W E40 others 840 12D ND NB

