



Essential LED

LED Spot 10W E27 6500K 230V R80 RCA

Essential LED is an affordable LED spot lamp that is suitable for replacing halogen spot lamps. It provides a natural lighting effect as well as instant energy savings – an environmentally friendly solution. The Philips Essential LED family is designed for spot and general lighting applications in the hospitality, retail and home segments.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	950 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	95.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Lamp Current (Nom)	65 mA


Wattage Equivalent	80 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	72 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	R80 [R 80mm]
Approval and Application	
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	10 kWh
Product Data	
Order product name	LED Spot 10W E27 6500K 230V R80 RCA
Full product name	LED Spot 10W E27 6500K 230V R80 RCA
Full product code	871869679811900

Essential LED

Order code	929001858187
Material Nr. (12NC)	929001858187
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696798119



Numerator - Packs per outer box	12
EAN/UPC - Case	8718696798126

Dimensional drawing



Product	D	C
LED Spot 10W E27 6500K 230V R80 RCA	80 mm	115 mm


Photometric data



Spectral Power Distribution Colour - LED Spot 10W E27 6500K 230V R80 RCA

Light Distribution Diagram - LED Spot 10W E27 6500K 230V R80 RCA

General Uniform Lighting



CalcLux Photonics 4.5



Philips Lighting B.V.

Page: 1/1

Accent Lighting Spots - LED Spot 10W E27 6500K 230V R80 RCA

Essential LED

Lifetime



Life Expectancy Diagram - LED Spot 10W E27 6500K 230V R80 RCA

Lumen Maintenance Diagram - LED Spot 10W E27 6500K 230V R80 RCA

