



MASTER Value Decorative LED bulbs

LED classic-giant 40W E27 T65 GOLD DIM

The new collection of MASTER Value Decorative LED bulbs will transform any home. decorative LED bulbs are ideal for decorative lighting projects, they offer a perfect blend of (warm) white light and a minimalistic lighting experience. With a very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you can enjoy soft and evenly distributed light. And thanks to the dimmable LED bulbs, you can dial it up or down to suit your mood. So, you can create a welcoming harmony in your space with decorative LED lamps that shine with trendy and stylish charm.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	820 [CCT of 2000K]
Color Code	820 [CCT of 2000K]
Luminous Flux	470 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	72.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80


LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 Hz
Input Frequency	50 Hz
Power Consumption	6.5 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	230 V
Temperature	
T-Case Maximum (Nom)	45 °C

MASTER Value Decorative LED bulbs

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Transparent amber
Bulb Shape	T65 [T 65mm]
Approval and Application	
Energy Consumption kWh/1000 h	7 kWh
EyeComfort	Yes
Product Data	
Order product name	LED classic-giant 40W E27 T65 GOLD DIM


Full product name	LED classic-giant 40W E27 T65 GOLD DIM
Full product code	871869680351600
Order code	929001873601
Material Nr. (12NC)	929001873601
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696803516
Numerator - Packs per outer box	2
EAN/UPC - Case	8718696803523

Dimensional drawing




Product	D	C
LED classic-giant 40W E27 T65 GOLD DIM	65 mm	273 mm

Photometric data




Light Distribution Diagram - LED classic-giant 40W E27 T65 GOLD DIM



Spectral Power Distribution Colour - LED classic-giant 40W E27 T65 GOLD DIM


MASTER Value Decorative LED bulbs

Photometric data




General uniform lighting - LED classic-giant 40W E27 T65 GOLD DIM

Lifetime



Lumen Maintenance Diagram - LED classic-giant 40W E27 T65 GOLD DIM



Life Expectancy Diagram - LED classic-giant 40W E27 T65 GOLD DIM

