



CorePro LEDtube EM/ Mains T8

CorePro LEDtube 1200mm HO 18W 865 T8

The CorePro LEDtube is an affordable LED solution suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	30000 h
Switching Cycle	200000X
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux (Nom)	2000 lm
Correlated Color Temperature (Nom)	6500 K
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	18 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Material	Glass
Product Length	1200 mm
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate


CorePro LEDtube EM/Mains T8

Energy Consumption kWh/1000 h	18 kWh
Product Data	
Full product code	871869680611100
Order product name	CorePro LEDtube 1200mm HO 18W 865 T8
EAN/UPC - Product	8718696806111
Order code	929001874802

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001874802
Net Weight (Piece)	0.215 kg

Warnings and Safety


Dimensional drawing




TLED 1200mm 18W-36W 2000lm 240D 6500K

Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm HO 18W 865 T8	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm

Photometric data




18W G13 865 6500K



18W G13 865 6500K


CorePro LEDtube EM/Mains T8

Photometric data




18W G13


Lifetime




18W G13



18W G13




18W G13



18W G13

CorePro LEDtube EM/Mains T8

Lifetime



18W G13

