



5.5PL-C/LED/13H/827/IF5/P/4P 20/1

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact flourescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Product data

G24Q [G24q]			
50,000 hour(s)			
50,000			
LED			
Yes			
827 [CCT of 2700K]			
150 degree(s)			
520 lm			
Warm White (WW)			
2700 K			
94.00 lm/W			
<6			
82			
70 %			
25000-100000 Hz			
25000-100000 Hz			
5.5 W			


Lamp Current (Max)	280 mA			
Lamp Current (Min)	130 mA			
Starting Time (Nom)	0.5 s			
Warm-up time to 60% light	0.5 s			
Power Factor (Fraction)	0.9			
Voltage (Nom)	14-60 V			
UL Type	Type A - works on ballast			
Temperature				
Ambient temperature range	-20 °C to 45 °C			
T-Case Maximum (Nom)	75 °C			
Controls and Dimming				
Dimmable	Yes			
Mechanical and Housing				
Bulb Material	Plastic			
Product Length	140 mm			
Bulb Shape	PL-C			
Approval and Application				
Energy Saving Product	Yes			

Datasheet, 2023, November 12 data subject to change

Approval Marks	RoHS compliance UL certificate
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	5.5PL-C/LED/13H/827/IF5/P/4P 20/1
Full product name	5.5PL-C/LED/13H/827/IF5/P/4P 20/1
Order code	929001885304


Material Nr. (12NC)	929001885304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677532390
Numerator - Packs per outer box	20
EAN/UPC - Case	50046677532395

Dimensional drawing




Product	D	D1	A1	A2	А3
5.5PL-C/LED/13H/827/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm

Photometric data






General uniform lighting - 5.5PL-C/LED/13H/827/IF5/P/4P 20/1




Spectral Power Distribution Colour - 5.5PL-C/LED/13H/827/IF5/P/4P 20/1


Light Distribution Diagram - 5.5PL-C/LED/13H/827/IF5/P/4P 20/1

Lifetime






Life Expectancy Diagram - 5.5PL-C/LED/13H/827/IF5/P/4P 20/1








Life Expectancy Diagram - 5.5PL-C/LED/13H/827/IF5/P/4P 20/1





Lumen Maintenance Diagram - 5.5PL-C/LED/13H/827/IF5/P/4P 20/1



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.