



# Classic filament LEDbulbs

## CLA LEDBulb ND 8-75W E27 827 A60 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Colour Code	827 [CCT of 2700K]
Luminous Flux	1,055 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	131.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz

Power Consumption	8 W
Lamp current (nom.)	70 mA
Wattage equivalent	75 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	48 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	A60 [A 60 mm]

# Classic filament LEDbulbs

## Approval and Application

Energy consumption kWh/1,000 hours 8 kWh

## Product Data

Order product name	CLA LEDBulb ND 8-75W E27 827 A60 CL
Full product name	CLA LEDBulb ND 8-75W E27 827 A60 CL
Full EOC	871869680951800
Order code	80951800

Material no. (12 NC) 929001888902


SAP numerator – quantity per pack 1

EAN/UPC – Product/Case 8718696809518

Numerator – packs per outer box 10


EAN/UPC - Case 8718696809525

## Dimensional drawing




Product	D	C
CLA LEDBulb ND 8-75W E27 827 A60 CL	60 mm	104 mm


## Photometric data



Spectral Power Distribution Colour - CLA LEDBulb ND 8-75W E27 827 A60 CL





General uniform lighting - CLA LEDBulb ND 8-75W E27 827 A60 CL



Light Distribution Diagram - CLA LEDBulb ND 8-75W E27 827 A60 CL

# Classic filament LEDbulbs

## Lifetime



Lumen Maintenance Diagram - CLA LEDBulb ND 8-75W E27 827 A60 CL

Life Expectancy Diagram - CLA LEDBulb ND 8-75W E27 827 A60 CL

