



# Classic filament LEDbulbs

## CLA LEDBulb ND 4-40W A60 E27 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	109.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	4.3 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.41
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	45 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60 [A 60mm]

Approval and Application	
Energy Consumption kWh/1000 h	5 kWh

# Classic filament LEDbulbs



EyeComfort	Yes
<b>Product Data</b>	
Order product name	CLA LEDBulb ND 4-40W A60 E27 827 CL
Full product name	CLA LEDBulb ND 4-40W A60 E27 827 CL
Full product code	871869963086700
Order code	929001890012

Material Nr. (12NC)	929001890012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699630867
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699630874

## Dimensional drawing

Product	D	C
CLA LEDBulb ND 4-40W A60 E27 827 CL	60 mm	104 mm

## Photometric data





General uniform lighting - CLA LEDBulb ND 4-40W A60 E27 827 CL

Spectral Power Distribution Colour - CLA LEDBulb ND 4-40W A60 E27 827 CL

Light Distribution Diagram - CLA LEDBulb ND 4-40W A60 E27 827 CL

# Classic filament LEDbulbs

## Lifetime



Life Expectancy Diagram - CLA LEDBulb ND 4-40W A60 E27 827 CL

Lumen Maintenance Diagram - CLA LEDBulb ND 4-40W A60 E27 827 CL

