



Classic filament LEDbulbs

CLA LEDBulb D 8-60W ST64 B22 827 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	B22 [B22]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	8-60W
Light Technical	
Colour Code	827 [CCT of 2,700 K]
Lamp Luminous Flux 25°C EL (Nom)	806 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	100.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	8 W
Lamp current (nom.)	52 mA

Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	50 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Clear
Approval and Application	
Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	8 kWh


Classic filament LEDbulbs

Product Data

Full product code	871869681429100
Order product name	CLA LEDBulb D 8-60W ST64 B22 827 CL
EAN/UPC – product	8718696814291
Order code	929001895602
Numerator – quantity per pack	1

Numerator – packs per outer box	6
Material no. (12NC)	929001895602
Net weight (piece)	0.048 kg


Dimensional drawing




Bulb ST64 230V 8-60W 806lm 2700K B22

Product	D	C
CLA LEDBulb D 8-60W ST64 B22 827 CL	64 mm	138 mm


Photometric data



LED Bulb CLA 8-60W B22 ST64 Clear 827 DIM




LED Bulb CLA 5.5-40W E27 ST64 Clear 827 DIM




LED Bulb CLA 8-60W B22 ST64 Clear 827 DIM

Classic filament LEDbulbs

Lifetime



LEDBulb CLA 5.5-40W E27 ST64 Clear 827 DIM



LEDBulb CLA 5.5-40W E27 ST64 Clear 827 DIM

