



# Classic filament LEDbulbs

## CLA LEDBulb D 8-60W ST64 B22 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap-Base	B22 [B22]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	8 W
Lamp Current (Nom)	52 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	ST64

# Classic filament LEDbulbs

## Approval and Application

Energy Consumption kWh/1000 h 8 kWh

## Product Data

Order product name	CLA LEDBulb D 8-60W ST64 B22 827 CL
Full product name	CLA LEDBulb D 8-60W ST64 B22 827 CL
Full product code	871869681429100
Order code	929001895602

Material Nr. (12NC) 929001895602


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8718696814291

Numerator - Packs per outer box 6



EAN/UPC - Case 8718696814307

## Dimensional drawing




Product	D	C
CLA LEDBulb D 8-60W ST64 B22 827 CL	64 mm	138 mm

## Photometric data



Light Distribution Diagram - CLA LEDBulb D 8-60W ST64 B22 827 CL



Spectral Power Distribution Colour - CLA LEDBulb D 8-60W ST64 B22 827 CL



General uniform lighting - CLA LEDBulb D 8-60W ST64 B22 827 CL

# Classic filament LEDbulbs

## Lifetime



Life Expectancy Diagram - CLA LEDBulb D 8-60W ST64 B22 827 CL

Lumen Maintenance Diagram - CLA LEDBulb D 8-60W ST64 B22 827 CL

