

Decorative LED candles and lustres

Classic LEDCandle D 5-32W BA35 E14 822 GOLD

The new Deco collection candles and lustres transforms your home with a perfect blend of warm white light and a lean, minimalistic lighting experience. With long lifetime, up to 90% energy savings, no flickering and an instant full-level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

Product data

General Information	
Cap base	E14 [E14]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	822 [CCT of 2200K]
Luminous Flux	350 lm
Colour designation	Flame
Correlated Colour Temperature	2200 K
Luminous efficacy (rated) (nom.)	70.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz

Power Consumption	5 W
Lamp current (nom.)	38 mA
Wattage equivalent	32 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	50 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Amber
Bulb shape	BA35

Decorative LED candles and lustres

Approval and Application


Energy consumption kWh/1,000 hours 5 kWh

Product Data

Order product name	CLA LEDCandle D 5-32W BA35 E14 822 GOLD
Full product name	Classic LEDCandle D 5-32W BA35 E14 822 GOLD
Full EOC	871869681443700


Order code	81443700
Material no. (12 NC)	929001896502
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696814437
Numerator – packs per outer box	10
EAN/UPC – Case	8718696814444

Dimensional drawing




Product	D	C
CLA LEDCandle D 5-32W BA35 E14 822 GOLD	35 mm	129 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDCandle D 5-32W BA35 E14 822 GOLD





General uniform lighting - CLA LEDCandle D 5-32W BA35 E14 822 GOLD



Light Distribution Diagram - CLA LEDCandle D 5-32W BA35 E14 822 GOLD

Decorative LED candles and lustres

Lifetime



Life Expectancy Diagram - CLA LEDCandle D 5-32W BA35 E14 822 GOLD

Lumen Maintenance Diagram - CLA LEDCandle D 5-32W BA35 E14 822 GOLD

