



MASTER Value Decorative LED bulbs

LED giant 25W E27 G200 4000K smoky D

The new collection of MASTER Value Decorative LED bulbs will transform any home. decorative LED bulbs are ideal for decorative lighting projects, they offer a perfect blend of (warm) white light and a minimalistic lighting experience. With a very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you can enjoy soft and evenly distributed light. And thanks to the dimmable LED bulbs, you can dial it up or down to suit your mood. So, you can create a welcoming harmony in your space with decorative LED lamps that shine with trendy and stylish charm.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Color Code	840 [CCT of 4000K]
Luminous Flux	270 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	41.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80


LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	6.5 W
Lamp Current (Nom)	45 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	45 °C

MASTER Value Decorative LED bulbs

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	G200 [G 200mm]
Approval and Application	
Energy Consumption kWh/1000 h	7 kWh
EyeComfort	Yes
Product Data	
Order product name	LED giant 25W E27 G200 4000K smoky D

Full product name	LED giant 25W E27 G200 4000K smoky D
Full product code	871869681506900
Order code	929001903101
Material Nr. (12NC)	929001903101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696815069
Numerator - Packs per outer box	2
EAN/UPC - Case	8718696815076

Dimensional drawing




Product	D	C
LED giant 25W E27 G200 4000K smoky D	200 mm	286 mm

Photometric data




Spectral Power Distribution Colour - LED giant 25W E27 G200 4000K smoky D



General uniform lighting - LED giant 25W E27 G200 4000K smoky D


MASTER Value Decorative LED bulbs

Photometric data




Light Distribution Diagram - LED giant 25W E27 G200 4000K smoky D

Lifetime



Life Expectancy Diagram - LED giant 25W E27 G200 4000K smoky D



Lumen Maintenance Diagram - LED giant 25W E27 G200 4000K smoky D

