



Decorative LED bulbs

LED giant 25W E27 T65 4000K smoky D

The new Deco collection (bulb) transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience. With very long lifetime, up to 90% energy savings, no flickering and an instant full-level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.


Product data

General Information		Temperature	
Cap base	E27 [E27]	Warm-up time to 60% light (nom.)	0.5 s
Nominal lifetime (nom.)	15000 h	Power factor (nom.)	0.7
Switching cycle	20000X	Voltage (Nom)	220-240 V
Technical type	6.5-25W	Temperature	
Light Technical		T-Case maximum (nom.)	45 °C
Colour Code	840 [CCT of 4,000 K]	Controls and Dimming	
Lamp Luminous Flux 25°C EL (Nom)	270 lm	Dimmable	Yes
Colour Designation	Cool White (CW)	Approval and Application	
Colour Temperature, horizontal (Nom)	4000 K	Energy efficiency label (EEL)	A
Lamp Luminous Efficacy EM (Nom)	41.00 lm/W	Energy Consumption kWh/1000 h	7 kWh
Colour consistency	<6	Product Data	
Colour Rendering Index, horiz (Nom)	80	Full product code	871869681512000
LLMF at end of nominal lifetime (nom.)	70 %	Order product name	LED giant 25W E27 T65 4000K smoky D
Operating and Electrical		EAN/UPC – product	8718696815120
Input frequency	50 to 60 Hz	Order code	929001903301
Power (Rated) (Nom)	6.5 W	Numerator – quantity per pack	1
Lamp current (nom.)	45 mA	Numerator – packs per outer box	2
Wattage equivalent	25 W	Material no. (12NC)	929001903301
Starting time (nom.)	0.5 s		

Decorative LED bulbs

Net weight (piece) 0.196 kg


Dimensional drawing




Bulb T65 230V 6-40W 470lm 2000K E27 D

Product	D	C
LED giant 25W E27 T65 4000K smoky D	65 mm	273 mm

Photometric data




LEDBulb giant 25W E27 G200 840 DIM



©2019 Philips Lighting B.V. Page: 1/1


LEDBulb giant 25W E27 T65 840 DIM




LEDBulb giant 25W E27 G200 840 DIM

Decorative LED bulbs

Lifetime



LEDBulb giant 25W E27 G200 840 DIM



LEDBulb giant 25W E27 G200 840 DIM

