



# TrueForce High Lumen PAR

## 23PAR30s/PER/930/S15/ND/120V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

### Product data


General Information		Power Consumption	
Cap-Base	E26 [Single Contact Medium Screw]	Power Consumption	23 W
Nominal lifetime	25,000 hour(s)	Lamp Current (Nom)	206 mA
Switching Cycle	50,000	Wattage Equivalent	75 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	930 [CCT of 3000K]	T-Case Maximum (Nom)	94 °C
Beam Angle (Nom)	15 degree(s)		
Luminous Flux	1,900 lm	Controls and Dimming	
Luminous Intensity (Nom)	12,000 cd	Dimmable	No
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	82.00 lm/W	Bulb Finish	Clear
Color Consistency	<4	Bulb Material	Aluminum
Color rendering index (CRI)	90	Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Approval and Application	
Line Frequency	50 to 60 Hz	Suitable For Accent Lighting	Yes
Input Frequency	50 to 60 Hz		

# TrueForce High Lumen PAR

Energy Consumption kWh/1000 h	- kWh
<b>Product Data</b>	
Order product name	23PAR30s/PER/930/S15/ND/120V 6/1FB
Full product name	23PAR30s/PER/930/S15/ND/120V 6/1FB
Order code	929001917404
Material Nr. (12NC)	929001917404



Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677534684
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677534689

## Dimensional drawing




Product	D	C
23PAR30s/PER/930/S15/ND/120V 6/1FB	96 mm	94 mm

## Photometric data



Spectral Power Distribution Colour - 23PAR30s/PER/930/S15/ND/120V 6/1FB



Accent Lighting Spots - 23PAR30s/PER/930/S15/ND/120V 6/1FB



Light Distribution Diagram - 23PAR30s/PER/930/S15/ND/120V 6/1FB

# TrueForce High Lumen PAR

## Lifetime



Life Expectancy Diagram - 23PAR30s/PER/930/S15/ND/120V 6/1FB

Lumen Maintenance Diagram - 23PAR30s/PER/930/S15/ND/120V 6/1FB

