



# CorePro LED PLS

## CorePro LED PLS 5W 830 2P G23 20/1

The Philips CorePro LED PLS integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplamplung in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environment-friendly.

### Product data


General Information	
Base	G23 [ G23]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	30000 h
Switching Cycle	50000X
Light Technical	
Color Code	830 [ CCT of 3000K]
Beam Angle (Nom)	120 °
Initial lumen (Nom)	520 lm
Correlated Color Temperature (Nom)	3000 K
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	5 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	220-240 V

Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	83 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Approbation Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	7 kWh
Product Data	
Order product name	CorePro LED PLS 5W 830 2P G23
EAN/UPC - Product	8718699596668
Order code	344309
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20

# CorePro LED PLS

Material Nr. (12NC)	929001926302
Net Weight (Piece)	0.043 kg


## Dimensional drawing




PLED PLS 220-240V 5-9W 475lm 3000K G23

Product	D	D1	A1	A2	A3
CorePro LED PLS 5W 830 2P G23	31.1 mm	15.8 mm	108 mm	144 mm	166 mm


## Photometric data



LEDtube CorePro PLS EM 5W G23 830 12D ND





LEDtub CorePro PLS EM 5W G23 830 12D ND



LEDtube CorePro PLS EM 5W G23 830 12D ND



# CorePro LED PLS

## Lifetime




LEDtube CorePro PLS EM 5W G23 830 12D ND

LEDtube CorePro PLS EM 5W G23 830 12D ND



LEDtube CorePro PLS EM 5W G23 830 12D ND

LEDtube CorePro PLS EM 5W G23 830 12D ND



LEDtube CorePro PLS EM 5W G23 830 12D ND

## CorePro LED PLS

