



Specialty Lamps

8A19/LED/RED/P/ND 120V 4/1FB

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data


General Information		Starting Time (Nom)		0.5 s
Cap-Base	E26 [Single Contact Medium Screw]	Warm-up time to 60% light		0.5 s
Nominal lifetime	10,950 hour(s)	Power Factor (Fraction)		0.5
Switching Cycle	20,000	Voltage (Nom)		120 V
Rated Lifetime (Hours)	10,950 hour(s)	Temperature		
Lighting Technology	LED	T-Case Maximum (Nom)		80 °C
EU RoHS compliant	Yes	Controls and Dimming		
Light Technical		Dimmable		No
Beam Angle (Nom)	120 degree(s)	Mechanical and Housing		
Color Consistency	-	Bulb Finish		Frosted
Color rendering index (CRI)	-	Bulb Material		Plastic
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape		A19
Operating and Electrical		Approval and Application		
Line Frequency	60 Hz	Energy Consumption kWh/1000 h		- kWh
Input Frequency	60 Hz	Energy Certifications		No
Power Consumption	8 W	EyeComfort		Yes
Lamp Current (Nom)	115 mA			
Wattage Equivalent	40 W			

Specialty Lamps

LED Innovations	EyeComfort
Product Data	
Order product name	8A19/LED/RED/P/ND 120V 4/1FB
Full product name	8A19/LED/RED/P/ND 120V 4/1FB
Order code	463273
Material Nr. (12NC)	929001997805



Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677463274
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677463279

Dimensional drawing




Product	D	C
8A19/LED/RED/P/ND 120V 4/1FB	60 mm	107 mm

Photometric data



Light Distribution Diagram - 8A19/LED/RED/P/ND 120V 4/1FB

General uniform lighting - 8A19/LED/RED/P/ND 120V 4/1FB




Spectral Power Distribution Colour - 8A19/LED/RED/P/ND 120V 4/1FB

Specialty Lamps

Lifetime



Lumen Maintenance Diagram - 8A19/LED/RED/P/ND 120V 4/1FB



Life Expectancy Diagram - 8A19/LED/RED/P/ND 120V 4/1FB

