



MASTER LEDspot LV AR111

MAS LED SpotLV 20-100W 927 AR111 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimizes maintenance cost without any reduction in brightness.

产品数据

一般資訊	
燈座基底	G53 [G53]
標稱使用壽命	25,000 h
切換週期	50,000
照明技術	LED
符合歐盟 RoHS 標準	是
照明技術	
色碼	927
光束角 (Nom)	24 °
光通量	1,200 lm
光強 (標稱)	4,000 cd
色彩名稱	暖白光 (WW)
相關色彩溫度 (規範)	2700 K


光效 (額定) (標準)	60.00 lm/W
色彩一致性	<4
演色性指數 (CRI)	91
LLMF 標稱壽命結束 (規範)	70 %
運轉與電力	
線路頻率	- Hz
輸入頻率	- Hz
耗電量	20 W
燈具電流 (標稱)	2,400 mA
相等瓦數	100 W
起始時間 (標稱)	0.5 s
達到 60% 光色的熱穩時間	0.5 s
功率因數 (比值)	0.7

MASTER LEDspot LV AR111

電壓 (標稱)	ac electronic 12 V
溫度	
環境溫度範圍	-20 °C 至 45 °C
T 盒上限 (正常情況)	80 °C
控制與調光	
可調光	是
機械與外罩	
燈泡形狀	AR111
認證與應用	
適合補強燈	是



能源消耗 kWh/1000 h	22 kWh
產品資料	
下訂產品名稱	MAS LED SpotLV 20-100W 927 AR111 24D
完整產品名稱	MAS LED SpotLV 20-100W 927 AR111 24D
完整產品代碼	871869969071700
訂單代碼	929002239808
材質 Nr. (12NC)	929002239808
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8718699690717
分子 - 每一外盒包裝	6
EAN/UPC - 箱	8718699690724

二维绘图



Product	D	C
MAS LED SpotLV 20-100W 927 AR111 24D	111 mm	62 mm

光度数据




Accent Lighting Spots - MAS LED SpotLV 20-100W 927 AR111 24D

Spectral Power Distribution Colour - MAS LED SpotLV 20-100W 927 AR111 24D


MASTER LEDspot LV AR111

光度数据



Light Distribution Diagram - MAS LED SpotLV 20-100W 927 AR111 24D

壽命



Life Expectancy Diagram - MAS LED SpotLV 20-100W 927 AR111 24D

Lumen Maintenance Diagram - MAS LED SpotLV 20-100W 927 AR111 24D

