

LED Corn Cobs

54CC/LED/830/ND EX39 BB 6/1

Philips Corn Cob HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	7,200 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	133.00 lm/W
Color Consistency	ANSI 3000K quadrangle
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	54 W
Starting Time (Nom)	2.5 s
Warm-up time to 60% light	2.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	Type B - bypass the ballast

Temperature	
T-Case Maximum (Nom)	194 °F

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	Corncob

Approval and Application	
Energy Consumption kWh/1000 h	54 kWh


Product Data	
Order product name	54CC/LED/830/ND EX39 BB 6/1
Full product name	54CC/LED/830/ND EX39 BB 6/1
Order code	557140
Material Nr. (12NC)	929002251514

LED Corn Cobs

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677557140
Numerator - Packs per outer box	6


EAN/UPC - Case	50046677557145

Dimensional drawing




Product	D	C
54CC/LED/830/ND EX39 BB 6/1	3-13/16 inch	9-13/16 inch


Photometric data



Spectral Power Distribution Colour - 54CC/LED/830/ND EX39 BB 6/1




Light Distribution Diagram - 54CC/LED/830/ND EX39 BB 6/1




Accent Lighting Spots - 54CC/LED/830/ND EX39 BB 6/1

LED Corn Cobs

Lifetime



Lumen Maintenance Diagram - 54CC/LED/830/ND EX39 BB 6/1



Life Expectancy Diagram - 54CC/LED/830/ND EX39 BB 6/1

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.