

# LED Designer Deco

## 8ST19/PER/927-922/CL/G/E26/WGX PF T20

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

### Product data

<b>General Information</b>		<b>Warm-up time to 60% light</b>		0.5 s
Cap-Base	E26 [Single Contact Medium Screw]	<b>Power Factor (Fraction)</b>		0.7
Nominal lifetime	15,000 hour(s)	<b>Voltage (Nom)</b>		120 V
Switching Cycle	20,000	<b>Temperature</b>		
Lighting Technology	LED	<b>T-Case Maximum (Nom)</b>		60 °C
EU RoHS compliant	Yes	<b>Controls and Dimming</b>		
<b>Light Technical</b>		<b>Mechanical and Housing</b>		
Color Code	927-922 [CCT of 2700K-2200K]	<b>Bulb Finish</b>		Clear
Beam Angle (Nom)	280 degree(s)	<b>Bulb Material</b>		Glass
Luminous Flux	800 lm	<b>Bulb Shape</b>		ST19
Color Designation	Warm Glow(WG)	<b>UL Wet/ damp/ dry location</b>		Wet location
Correlated Color Temperature (Nom)	2700 2200 K	<b>Approval and Application</b>		
Luminous Efficacy (rated) (Nom)	100.00 lm/W	<b>Energy Consumption kWh/1000 h</b>		- kWh
Color Consistency	<4	<b>Energy Certifications</b>		No
Color rendering index (CRI)	90	<b>T20 compliant</b>		Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %	<b>Application Conditions</b>		
<b>Operating and Electrical</b>		<b>can it be used in closed luminaires</b>		No
Line Frequency	60 Hz			
Input Frequency	60 Hz			
Power Consumption	8 W			
Lamp Current (Nom)	85 mA			
Wattage Equivalent	40 W			
Starting Time (Nom)	0.5 s			


Product Data	
Order product name	8ST19/PER/927-922/CL/G/E26/WGX PF T20
Full product name	8ST19/PER/927-922/CL/G/E26/WGX PF T20
Order code	929002296003
Material Nr. (12NC)	929002296003
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	046677556532
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677556537


Dimensional drawing

Product	D	C
8ST19/PER/927-922/CL/G/E26/WGX PF T20	64 mm	143 mm


Photometric data



Spectral Power Distribution Colour - 8ST19/PER/927-922/CL/G/E26/WGX PF T20



Light Distribution Diagram - 8ST19/PER/927-922/CL/G/E26/WGX PF T20



General uniform lighting - 8ST19/PER/927-922/CL/G/E26/WGX PF T20

Lifetime



Life Expectancy Diagram - 8ST19/PER/927-922/CL/G/E26/WGX PF T20



Lumen Maintenance Diagram - 8ST19/PER/927-922/CL/G/E26/WGX PF T20

