



# Tornado High Lumen

## Tornado High Lumen 60W WW E27 1CT/6

Energy saving lamp in spiral shape, with superior performance (long life, high switching) and high lumen warm bright light. Perfectly suitable to be used in places where high lumen is required, and the lamp is directly visible.

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Product data

General Information		LLMF At End Of Nominal Lifetime (Nom)	
Cap-Base	E27 [E27]		60 %
Nominal lifetime	10,000 hour(s)	Operating and Electrical	
Switching Cycle	10,000	Line Frequency	50 or 60 Hz
Rated Lifetime (Hours)	10,000 hour(s)	Input Frequency	50 or 60 Hz
Lighting Technology	Compact Fluorescent Integrated	Power Consumption	60.0 W
Light Technical		Lamp Current (Nom)	270 mA
Color Code	827 [CCT of 2700K]	Starting Time (Nom)	1.5 s
Luminous Flux	4,300 lm	Warm-up time to 60% light	10-60 s s
Color Designation	Warm White (WW)	Power Factor (Fraction)	0.92
Chromaticity Coordinate X (Nom)	463	Voltage (Nom)	220-240 V
Chromaticity Coordinate Y (Nom)	420	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	71.63 lm/W		
Color rendering index (CRI)	80		

## Tornado High Lumen

### Mechanical and Housing

Bulb Shape Spiral

### Approval and Application

Mercury (Hg) Content (Max) 5 mg

Energy Consumption kWh/1000 h 60 kWh

### Product Data

Order product name Tornado High Lumen 60W WW E27 1CT/6

Full product name Tornado High Lumen 60W WW E27 1CT/6

Full product code 872790080824700

Order code 80824700

Material Nr. (12NC) 929676006001


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8727900808247

Numerator - Packs per outer box 6

EAN/UPC - Case 8727900808254

## Dimensional drawing



Product	C (max)	F (max)	D (max)
Tornado High Lumen 60W WW E27 1CT/6	262 mm	88.1 mm	102 mm

