



Tornado High Lumen

Tornado High Lumen 60W WW E27 1CT/6

Energy saving lamp in spiral shape, with superior performance (long life, high switching) and high lumen warm bright light. Perfectly suitable to be used in places where high lumen is required, and the lamp is directly visible.

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data


General Information		LLMF At End Of Nominal Lifetime (Nom)	
Cap-Base	E27	60 %	
Nominal lifetime	10,000 hour(s)		
Switching Cycle	10,000		
Rated Lifetime (Hours)	10,000 hour(s)		
Lighting Technology	Compact Fluorescent Integrated		
Light Technical		Operating and Electrical	
Color Code	827 [CCT of 2700K]	Line Frequency	50 or 60 Hz
Luminous Flux	4,300 lm	Input Frequency	50 or 60 Hz
Color Designation	Warm White (WW)	Power Consumption	60.0 W
Chromaticity Coordinate X (Nom)	463	Lamp Current (Nom)	270 mA
Chromaticity Coordinate Y (Nom)	420	Starting Time (Nom)	1.5 s
Correlated Color Temperature (Nom)	2700 K	Warm-up time to 60% light	10-60 s s
Luminous Efficacy (rated) (Nom)	71.63 lm/W	Power Factor (Fraction)	0.92
Color rendering index (CRI)	80	Voltage (Nom)	220-240 V
		Controls and Dimming	
		Dimmable	No

Tornado High Lumen

Mechanical and Housing	
Bulb Shape	Spiral
Approval and Application	
Mercury (Hg) Content (Max)	5 mg
Energy Consumption kWh/1000 h	60 kWh
Product Data	
Order product name	Tornado High Lumen 60W WW E27 1CT/6
Full product name	Tornado High Lumen 60W WW E27 1CT/6

Full product code	872790080824700
Order code	80824700
Material Nr. (12NC)	929676006001
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900808247
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900808254

Dimensional drawing



Product	C (max)	F (max)	D (max)
Tornado High Lumen 60W WW E27 1CT/6	262 mm	88.1 mm	102 mm

