



Tornado High Lumen

Tornado High Lumen 75W WW E40 1CT/6

Energy saving lamp in spiral shape, with superior performance (long life, high switching) and high lumen warm bright light. Perfectly suitable to be used in places where high lumen is required, and the lamp is directly visible.

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data

General Information	
Cap-Base	E40
Nominal lifetime	10,000 hour(s)
Switching Cycle	10,000
Rated Lifetime (Hours)	10,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	5,550 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	73.96 lm/W
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	60 %
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	75.0 W
Lamp Current (Nom)	350 mA
Starting Time (Nom)	1.5 s
Power Factor (Fraction)	0.92
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Spiral

Tornado High Lumen

Approval and Application	
Mercury (Hg) Content (Max)	5 mg
Energy Consumption kWh/1000 h	75 kWh
Product Data	
Order product name	Tornado High Lumen 75W WW E40 1CT/6
Full product name	Tornado High Lumen 75W WW E40 1CT/6
Full product code	872790080832200

Order code	929676006301
Material Nr. (12NC)	929676006301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900808322
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900808339

Dimensional drawing

Product	C (max)	F (max)	D (max)
Tornado High Lumen 75W WW E40 1CT/6	293 mm	88.1 mm	102 mm

