



# Tornado T2

## Tornado T2 15W WW E27 220-240V 1PF/6

Tornado has outstanding brightness which makes your colors appear more Vivid. It fits everywhere due to its compact design With comprehensive product range, it allows easy replacement of incandescent lamps all the way

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Product data

General Information		LLMF At End Of Nominal Lifetime (Nom)	
Cap-Base	E27		65 %
Nominal lifetime	10,000 hour(s)	Operating and Electrical	
Switching Cycle	10,000	Line Frequency	50 or 60 Hz
Rated Lifetime (Hours)	10,000 hour(s)	Input Frequency	50 or 60 Hz
Lighting Technology	Compact Fluorescent Integrated	Power Consumption	15.0 W
Light Technical		Lamp Current (Nom)	110 mA
Color Code	827 [CCT of 2700K]	Starting Time (Nom)	0.3 s
Luminous Flux	970 lm	Power Factor (Fraction)	0.6
Color Designation	Warm White (WW)	Voltage (Nom)	220-240 V
Chromaticity Coordinate X (Nom)	463	Controls and Dimming	
Chromaticity Coordinate Y (Nom)	420	Dimmable	No
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	65 lm/W	Bulb Shape	Spiral
Color rendering index (CRI)	82		


# Tornado T2

<b>Approval and Application</b>	
Mercury (Hg) Content (Max)	2.0 mg
Mercury (Hg) Content (Nom)	1.5 mg
Energy Consumption kWh/1000 h	15 kWh

<b>Product Data</b>	
Order product name	TORNADO T2 15,0W/827 E27 *
Full product name	Tornado T2 15W WW E27 220-240V 1PF/6
Full product code	872790092578400

Order code	92578400
Material Nr. (12NC)	929689114708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900925784
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900925791

## Dimensional drawing



Product	D (max)	C (max)	F (max)
TORNADO T2 15,0W/827 E27 *	51.5 mm	107.5 mm	42.5 mm

