



Tornado T2

Tornado T2 20W CDL E27 220-240V 1PF/6

Tornado has outstanding brightness which makes your colors appear more Vivid. It fits everywhere due to its compact design With comprehensive product range, it allows easy replacement of incandescent lamps all the way

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data

General Information		LLMF At End Of Nominal Lifetime (Nom)	65 %
Cap-Base	E27 [E27]		
Nominal lifetime	10,000 hour(s)	Operating and Electrical	
Switching Cycle	10,000	Line Frequency	50 or 60 Hz
Rated Lifetime (Hours)	10,000 hour(s)	Input Frequency	50 or 60 Hz
Lighting Technology	Compact Fluorescent Integrated	Power Consumption	20.0 W
		Lamp Current (Nom)	150 mA
Light Technical		Starting Time (Nom)	0.3 s
Color Code	865 [CCT of 6500K]	Warm-up time to 60% light	5-40 s s
Luminous Flux	1,305 lm	Power Factor (Fraction)	0.6
Color Designation	Cool Daylight	Voltage (Nom)	220-240 V
Chromaticity Coordinate X (Nom)	313		
Chromaticity Coordinate Y (Nom)	337	Controls and Dimming	
Correlated Color Temperature (Nom)	6500 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	64 lm/W		
Color rendering index (CRI)	80		

Tornado T2

Mechanical and Housing			
Bulb Shape	Spiral		
Approval and Application			
Mercury (Hg) Content (Max)	2.0 mg		
Mercury (Hg) Content (Nom)	1.5 mg		
Energy Consumption kWh/1000 h	20 kWh		
Product Data			
Order product name	Tornado T2 20W CDL E27 220-240V 1PF/6		

Full product name	Tornado T2 20W CDL E27 220-240V 1PF/6	
Full product code	871016340515500	
Order code	40515500	
Material Nr. (12NC)	929689115001	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8710163405155	
Numerator - Packs per outer box	6	
EAN/UPC - Case	8710163405162	

Dimensional drawing



Product	D (max)	C (max)	F (max)
Tornado T2 20W CDL E27 220-240V 1PF/6	56.5 mm	116.0 mm	47 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.