



Economy stick

Economy Stick 11W WW E27 220-240 1PF/6

Entry non-covered energy saving lamp, Long life with low energy consumption.
Product consists of Philips quality at everyday low price

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	6,000 hour(s)
Switching Cycle	6,000
Rated Lifetime (Hours)	6,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	660 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	59 lm/W
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	11.0 W
Lamp Current (Nom)	80 mA
Starting Time (Nom)	0.3 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Stick
Approval and Application	
Mercury (Hg) Content (Max)	2.0 mg
Mercury (Hg) Content (Nom)	1.5 mg

Economy stick

Energy Consumption kWh/1000 h	11 kWh
Product Data	
Order product name	Economy Stick 11W WW E27 220-240 1PF/6
Full product name	Economy Stick 11W WW E27 220-240 1PF/6
Full product code	871829165853500
Order code	65853500

Material Nr. (12NC)	929689116501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291658535
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291658542

Dimensional drawing



Product	D (max)	C (max)	F (max)
Economy Stick 11W WW E27 220-240 1PF/6	21.7 mm	138 mm	40.4 mm

