



MASTER PL-Electronic

MASTER PLE-R 15W/827 E27 220-240V 1CT/6

Non-covered energy-saving MASTER lamps for professional use

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data

General Information		LLMF At End Of Nominal Lifetim	LLMF At End Of Nominal Lifetime (Nom) 65 %		
Cap-Base	E27 [E27]				
Nominal lifetime	20,000 hour(s)	Operating and Electrical			
Switching Cycle	50,000	Line Frequency	50 or 60 Hz		
Rated Lifetime (Hours)	20,000 hour(s)	Input Frequency	50 or 60 Hz		
Lighting Technology	Compact Fluorescent Integrated	Power Consumption	15.0 W		
		Lamp Current (Nom)	110 mA		
Light Technical		Starting Time (Nom)	1.0 s		
Color Code	827 [CCT of 2700K]	Power Factor (Fraction)	0.6		
Luminous Flux	890 lm	Voltage (Nom)	220-240 V		
Color Designation	Warm White (WW)				
Chromaticity Coordinate X (Nom)	463	Controls and Dimming			
Chromaticity Coordinate Y (Nom)	420	Dimmable	No		
Correlated Color Temperature (Nom)	2700 K				
Luminous Efficacy (rated) (Nom)	58.3 lm/W	Mechanical and Housing			
Color rendering index (CRI)	82	Bulb Shape	Stick		

MASTER PL-Electronic

Approval and Application	
Mercury (Hg) Content (Max)	1.5 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	15 kWh
Product Data	

871150075142310

MASTER PLE-R 15W/827 E27 220-240V 1CT/6

MASTER PLE-R 15W/827 E27 220-240V 1CT/6

Order code	75142310
Material Nr. (12NC)	929689132101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500751423
Numerator - Packs per outer box	6
EAN/UPC - Case	8711500761392

Dimensional drawing

Order product name

Full product name

Full product code



Product	D (max)	C (max)	F (max)
MASTER PLE-R 15W/827 E27 220-240V 1CT/6	39.6 mm	126.2 mm	48 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 30 - data subject to change