



# Tornado T2

## Tornado T2 12W WW E14 220-240V 1PF/6

Tornado has outstanding brightness which makes your colors appear more Vivid. It fits everywhere due to its compact design With comprehensive product range, it allows easy replacement of incandescent lamps all the way

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Product data


General Information		LLMF At End Of Nominal Lifetime (Nom)	
Cap-Base	E14 [E14]	65 %	
Nominal lifetime	10,000 hour(s)		
Switching Cycle	10,000		
Rated Lifetime (Hours)	10,000 hour(s)		
Lighting Technology	Compact Fluorescent Integrated		
Light Technical		Operating and Electrical	
Color Code	827 [CCT of 2700K]	Line Frequency	50 or 60 Hz
Luminous Flux	741 lm	Input Frequency	50 or 60 Hz
Color Designation	Warm White (WW)	Power Consumption	12.0 W
Chromaticity Coordinate X (Nom)	463	Lamp Current (Nom)	90 mA
Chromaticity Coordinate Y (Nom)	420	Starting Time (Nom)	0.3 s
Correlated Color Temperature (Nom)	2700 K	Warm-up time to 60% light	5-40 s s
Luminous Efficacy (rated) (Nom)	61 lm/W	Power Factor (Fraction)	0.6
Color rendering index (CRI)	82	Voltage (Nom)	220-240 V
		Controls and Dimming	
		Dimmable	No

# Tornado T2

Mechanical and Housing	
Bulb Shape	Spiral
Approval and Application	
Mercury (Hg) Content (Max)	2.0 mg
Mercury (Hg) Content (Nom)	1.5 mg
Energy Consumption kWh/1000 h	12 kWh
Product Data	
Order product name	Tornado T2 12W WW E14 220-240V 1PF/6

Full product name	Tornado T2 12W WW E14 220-240V 1PF/6
Full product code	871829111724700
Order code	11724700
Material Nr. (12NC)	929689134506
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291117247
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291117254

## Dimensional drawing



Product	D (max)	C (max)	F (max)
Tornado T2 12W WW E14 220-240V 1PF/6	47.5 mm	104.0 mm	40.5 mm

