



# **Economy stick**

# Economy Stick 23W WW E27 220-240 1PF/6

Entry non-covered energy saving lamp, Long life with low energy consumption. Product consists of Philips quality at everyday low price

### **Warnings and Safety**

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

#### **Product data**

General Information			
Cap-Base	E27 [E27]		
Nominal lifetime	6,000 hour(s)		
Switching Cycle	6,000		
Rated Lifetime (Hours)	6,000 hour(s)		
Lighting Technology	Compact Fluorescent Integrated		
Light Technical			
Color Code	827 [CCT of 2700K]		
Luminous Flux	1,430 lm		
Color Designation	Warm White (WW)		
Chromaticity Coordinate X (Nom)	463		
Chromaticity Coordinate Y (Nom)	420		
Correlated Color Temperature (Nom)	2700 K		
Luminous Efficacy (rated) (Nom)	62 lm/W		
Color rendering index (CRI)	82		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	23.0 W
Lamp Current (Nom)	160 mA
Starting Time (Nom)	0.3 s
Warm-up time to 60% light	5-40 s s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Stick
Approval and Application	
Mercury (Hg) Content (Max)	2.0 mg


Datasheet, 2023, April 15 data subject to change

## **Economy stick**

Mercury (Hg) Content (Nom)	1.5 mg			
Energy Consumption kWh/1000 h	23 kWh			
Product Data				
Order product name	Economy Stick 23W WW E27 220-240 1PF/6			
Full product name	Economy Stick 23W WW E27 220-240 1PF/6			
Full product code	871829121683400			
Order code	21683400			

Material Nr. (12NC)	929689156101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291216834
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291216841
'	

## Dimensional drawing



Product	D (max)	C (max)	F (max)
Economy Stick 23W WW E27 220-240 1PF/6	36.0 mm	160 mm	48.4 mm

